



Helio A6

ORDER FORM - MANITOBA POSSIBLE

1- Purchasing information

P.O. number:* _____ Date: _____
 Company Name:* _____
 Purchasing contact:* _____
 Phone:* _____
 Email:* _____
 Contact preference:* Phone Email
 Marked for: _____

3- Shipping information

Ship to:* **Manitoba Wheelchair Program**
 Name: _____
 Address: **1857 Notre Dame Ave.**
 City: **Wpg** Province: **MB**
 Postal Code: **R3E 3E7**
 Phone: **204-975-3250**

NC = NO CHARGE (option available through Manitoba Possible)
J = JUSTIFICATION REQUIRED (provide clinical rationale)
OTP = OPTION TO PURCHASE (client responsible for cost)
N/A = NOT AVAILABLE (option not available through Manitoba Possible)

MA080
 English Manual (STD)

Taxes not included

| MODEL | | | | | | | | | |
|--------------------------------|--------------------------|---|---|---|---|---|--|----|----|
| WC19 | <input type="checkbox"/> | Ultralight folding Helio A6 Wheelchair - 6000 series aluminum (265lb weight capacity) | | | | | | | NC |
| WC09 | <input type="checkbox"/> | HD Heavy duty kit (350 lb weight capacity) | | | | | | | NC |
| Frame | | | | | | | | | |
| SEAT WIDTH ³ | | | | | | | | | |
| SW | <input type="checkbox"/> | 14" <input type="checkbox"/> | 15" <input type="checkbox"/> | 16" <input type="checkbox"/> | 17" <input type="checkbox"/> | 18" ¹ <input type="checkbox"/> | | NC | |
| | <input type="checkbox"/> | 19" ¹ <input type="checkbox"/> | 20" ¹ <input type="checkbox"/> | 21" ² <input type="checkbox"/> | 22" ² <input type="checkbox"/> | | | NC | |
| SEAT DEPTH | | | | | | | | | |
| SD | <input type="checkbox"/> | 14" <input type="checkbox"/> | 15" <input type="checkbox"/> | 16" <input type="checkbox"/> | 17" <input type="checkbox"/> | 18" <input type="checkbox"/> | | NC | |
| | <input type="checkbox"/> | 19" <input type="checkbox"/> | 20" <input type="checkbox"/> | | | | | NC | |
| TRANSIT TIE DOWN | | | | | | | | | |
| AC04 | <input type="checkbox"/> | Transit Tie Down (Unoccupied) ⁴ | | | | | | | NC |
| AC05-S | <input type="checkbox"/> | WC-19 Transit Tie Down w/Q'straint belt ⁵ Short belt 20"-41" | | | | | | | J |
| AC05-L | <input type="checkbox"/> | WC-19 Transit Tie Down w/Q'straint belt ⁵ Long belt 20"-46" | | | | | | | J |
| AC35 | <input type="checkbox"/> | WC-19 Transit Tie Down without belt ⁵ | | | | | | | NC |

1- Available with HD Kit (350 lb) 2- Only with HD Kit (350 lb) 3. [Width calculator](#)
 4- required when ordering HD; 5- May interfere with swing away armrest and Clamp on height adjustable push handle; Not available with HD option

A6 FRONT Seat-to-floor Height - Please select your choice

| Forks / Position | | 3" caster (OTP) | | | 4" caster (OTP) | | | 5" caster (J) | | | 6" caster (NC) | | | 7" caster (OTP) | | | 8" caster (NC) | | |
|------------------|----|------------------|---------|---------|------------------|---------|---------|------------------|---------|---------|------------------|---------|---------|------------------|---------|---------|------------------|---------|---------|
| | | Stem bolt Length | | | Stem bolt Length | | | Stem bolt Length | | | Stem bolt Length | | | Stem bolt Length | | | Stem bolt Length | | |
| | | STD | +1" | +2" | STD | +1" | +2" | STD | +1" | +2" | STD | +1" | +2" | STD | +1" | +2" | STD | +1" | +2" |
| 4" | P1 | 12" | 13" | 14" | 12 1/2" | 13 1/2" | 14 1/2" | | | | | | | | | | | | |
| | P2 | 12 1/2" | 13 1/2" | 14 1/2" | 13" | 14" | 15" | 13 1/2" | 14 1/2" | 15 1/2" | | | | | | | | | |
| 5" | P1 | | | | | | | | | | | | | | | | | | |
| | P2 | | | | 13" | 14" | 15" | 13 1/2" | 14 1/2" | 15 1/2" | | | | | | | | | |
| | P3 | 13" | 14" | 15" | 13 1/2" | 14 1/2" | 15 1/2" | 14" | 15" | 16" | 14 1/2" | 15 1/2" | 16 1/2" | | | | | | |
| | P4 | 13 1/2" | 14 1/2" | 15 1/2" | 14" | 15" | 16" | 14 1/2" | 15 1/2" | 16 1/2" | 15" | 16" | 17" | 15 1/2" | 16 1/2" | 17 1/2" | | | |
| 7" | P1 | | | | | | | | | | 15 1/2" | 16 1/2" | 17 1/2" | 16" | 17" | 18" | | | |
| | P2 | | | | | | | 15 1/2" | 16 1/2" | 17 1/2" | 16" | 17" | 18" | 16 1/2" | 17 1/2" | 18 1/2" | | | |
| | P3 | | | | | | | 16" | 17" | 18" | 16 1/2" | 17 1/2" | 18 1/2" | 17" | 18" | 19" | 17 1/2" | 18 1/2" | 19 1/2" |
| | P4 | 15 1/2" | 16 1/2" | 17 1/2" | 16" | 17" | 18" | 16 1/2" | 17 1/2" | 18 1/2" | 17" | 18" | 19" | 17 1/2" | 18 1/2" | 19 1/2" | 18" | 19" | 20" |
| | P5 | 16" | 17" | 18" | 16 1/2" | 17 1/2" | 18 1/2" | 17" | 18" | 19" | 17 1/2" | 18 1/2" | 19 1/2" | 18" | 19" | 20" | 18 1/2" | 19 1/2" | 20 1/2" |

Height available +/- 1/4" (see stem bolt and fork combination at the end of the order form)

| CASTERS | | | Availability | | |
|--------------------|--------------------------|---|------------------------|--|-----|
| CA01-03 to CA01-08 | <input type="checkbox"/> | Composite wheel w/ PU tire (1") | 3", 4", 5", 6", 7", 8" | | NC |
| CA10 to CA11 | <input type="checkbox"/> | Pneumatic casters (1 ¼") | 6", 8" | | OTP |
| CA14 to CA16 | <input type="checkbox"/> | Newton UltraCaster Composite (1 ½ ") | 4", 5", 6" | | J |
| CA17 to CA19 | <input type="checkbox"/> | Newton UltraCaster Aluminum (1 ½ ") | 4", 5", 6" | | OTP |
| CASTER OPTIONS | | | | | |
| CA12 | <input type="checkbox"/> | Caster Pin Locks (Available with +1" or +2" Stem bolt ONLY) ¹ | | | OTP |
| CA13 | <input type="checkbox"/> | Carbon fiber Frog Legs suspension forks (Not available with caster pin locks) | | | OTP |

1- Not available with WC-19

Helio A6 - REAR Seat-to-floor Height - Please select your choice

| 20" (451) (NC) | 22" (501) (NC) | 24" (540) (NC) | 25" (559) (OTP) | 26" (590) (OTP) |
|----------------|----------------|----------------|-----------------|-----------------|
| 12" | 13" | 13 3/4" | 14 1/4" | 14 3/4" |
| 12 1/2" | 13 1/2" | 14 1/4" | 14 3/4" | 15 1/4" |
| 13" | 14" | 14 3/4" | 15 1/4" | 15 3/4" |
| 13 1/2" | 14 1/2" | 15 1/4" | 15 3/4" | 16 1/4" |
| 14" | 15" | 15 3/4" | 16 1/4" | 16 3/4" |
| 14 1/2" | 15 1/2" | 16 1/4" | 16 3/4" | 17 1/4" |
| 15" | 16" | 16 3/4" | 17 1/4" | 17 3/4" |
| 15 1/2" | 16 1/2" | 17 1/4" | 17 3/4" | 18 1/4" |
| 16" | 17" | 17 3/4" | 18 1/4" | 18 3/4" |
| 16 1/2" | 17 1/2" | 18 1/4" | 18 3/4" | 19 1/4" |
| 17" | 18" | 18 3/4" | 19 1/4" | 19 3/4" |
| 17 1/2" | 18 1/2" | 19 1/4" | 19 3/4" | 20 1/4" |

Configuration used: 1" seat slope with a center of gravity at 2"

Note: Tire size, center of gravity setting and seat slope may result in a variation of +/- ½" of selected seat to floor height"

| Footrest | | | | | |
|-----------------------------|--------------------------|--|--------------|-----------|-----|
| SWING-IN/SWING-OUT FOOTREST | | | | | |
| FR03-01 | <input type="checkbox"/> | 60° Swing-in/swing-out footrest - 13.5" - 17" | | Set at: * | NC |
| FR03-02 | <input type="checkbox"/> | 60° Swing-in/swing-out footrest - 14.5" - 19.5" | | Set at: * | NC |
| FR03-03 | <input type="checkbox"/> | 60° Swing-in/swing-out footrest - 15.5" - 20.5" | | Set at: * | NC |
| FR04-01 | <input type="checkbox"/> | 70° Swing-in/swing-out footrest - 13.5" - 17" | | Set at: * | NC |
| FR04-02 | <input type="checkbox"/> | 70° Swing-in/swing-out footrest - 14.5" - 19.5" | | Set at: * | NC |
| FR04-03 | <input type="checkbox"/> | 70° Swing-in/swing-out footrest - 15.5" - 20.5" | | Set at: * | NC |
| FR15-01 | <input type="checkbox"/> | 80° Swing-in/swing-out footrest - 13.5" - 16" ⁵ | | Set at: * | NC |
| FR15-02 | <input type="checkbox"/> | 80° Swing-in/swing-out footrest - 14.5" - 19.5" ⁵ | | Set at: * | NC |
| FR15-03 | <input type="checkbox"/> | 80° Swing-in/swing-out footrest - 15.5" - 20.5" ⁵ | | Set at: * | NC |
| FR06 | <input type="checkbox"/> | 90° swing-in/swing-out with front mount - Standard (no extension) ¹ | 7.5" - 11" | Set at: * | NC |
| FR07 | <input type="checkbox"/> | 90° swing-in/swing-out with front mount - Short extension ^{2, 1, 2} | 9.5" - 13" | Set at: * | NC |
| FR08 | <input type="checkbox"/> | 90° swing-in/swing-out with front mount - Medium extension ^{4, 1, 2} | 9.5" - 14.5" | Set at: * | NC |
| FOOTREST OPTIONS | | | | | |
| FR09 | <input type="checkbox"/> | High mount (footplate attached to the hanger with clamps) ³ | 5" - 13.5" | Set at: * | J |
| FR10 | <input type="checkbox"/> | Elevating legrest with calf pad, Length adjustable ⁴ Left <input type="checkbox"/> Right <input type="checkbox"/> | 14" - 22" | Set at: | J |
| FR99 | <input type="checkbox"/> | Omit Footrest | | | N/A |

1- Available only with two piece adjustable footplates; 2- May interfere with front casters; 3- Not available with front mount and the elevating legrest; * +/- 1/2"

4- The elevating legrest replace the footrest side selected; Not available with one piece footplate; 5- Not available with 8" caster

| FOOTPLATES | | | |
|-----------------------|-------------------------------------|---|-----|
| FP01 | <input type="checkbox"/> | Standard - Composite ¹ | NC |
| FP02 | <input type="checkbox"/> | Newton adjustable angle - Composite | J |
| FP03 | <input type="checkbox"/> | Newton adjustable angle - Aluminum | OTP |
| FP06 | <input type="checkbox"/> | One piece adjustable angle flip-up - Aluminum | OTP |
| FOOTPLATE ACCESSORIES | | | |
| FP08 | <input checked="" type="checkbox"/> | Length adjustable heel loop ² | NC |
| FP09 | <input type="checkbox"/> | Calf strap | OTP |
| FP30 | <input type="checkbox"/> | Bodypoint Aeromesh Padded calf strap | OTP |

1- Not available with front mount; 2- not available with one piece footplate

| SWING AWAY RESIDUAL LIMB SUPPORT | | | | |
|----------------------------------|--------------------------|--|--|-----|
| FR27 | <input type="checkbox"/> | Residual limb support - flat 6"x8" | Left <input type="checkbox"/> Right <input type="checkbox"/> | OTP |
| FR28 | <input type="checkbox"/> | Residual limb support - flat 8"x10" | Left <input type="checkbox"/> Right <input type="checkbox"/> | OTP |
| FR29 | <input type="checkbox"/> | Residual limb support - flat 10"x10" | Left <input type="checkbox"/> Right <input type="checkbox"/> | OTP |
| FR30 | <input type="checkbox"/> | Residual limb support - flat 10"x14" | Left <input type="checkbox"/> Right <input type="checkbox"/> | OTP |
| FR32 | <input type="checkbox"/> | Residual limb support - contour 6"x8" | Left <input type="checkbox"/> Right <input type="checkbox"/> | OTP |
| FR33 | <input type="checkbox"/> | Residual limb support - contour 8"x10" | Left <input type="checkbox"/> Right <input type="checkbox"/> | OTP |

Backrest

| FIXED ANGLE BACK CANES WITH INTEGRATED PUSH HANDLE (push handle included - no further selection needed) | | | | | |
|---|--------------------------|-----------------------------|-----------------------------|-----------------------|----|
| BC58-915 | <input type="checkbox"/> | Straight aluminum back cane | 9" - 15" increment of 1/2" | Set at ² : | NC |
| BC58-1521 | <input type="checkbox"/> | Straight aluminum back cane | 15" - 21" increment of 1/2" | Set at ² : | NC |
| BC60 | <input type="checkbox"/> | Straight aluminum back cane | 21" - 24" increment of 1" | Set at ² : | J |
| BC01-16 | <input type="checkbox"/> | 8° bend aluminum back cane | 16" | | NC |
| BC01-18 | <input type="checkbox"/> | 8° bend aluminum back cane | 18" | | NC |
| BC01-20 | <input type="checkbox"/> | 8° bend aluminum back cane | 20" | | NC |
| BC59 | <input type="checkbox"/> | 8° bend aluminum back cane | 21" - 24" increment of 1" | Set at ² : | J |

| FIXED ANGLE, HEIGHT ADJUSTABLE BACK CANES WITH PUSH HANDLE OPTIONS (MUST select ONE push handle options) | | | | | |
|--|--------------------------|-----------------------------|-------------------------------|-----------------------|-----|
| BC11-912 | <input type="checkbox"/> | Straight aluminum back cane | 9" - 12" increment of 1/2" | Set at ² : | J |
| BC11-1215 | <input type="checkbox"/> | Straight aluminum back cane | 12" - 15" increment of 1/2" | Set at ² : | J |
| BC11-1518 | <input type="checkbox"/> | Straight aluminum back cane | 15" - 18" increment of 1/2" | Set at ² : | J |
| BC11-1821 | <input type="checkbox"/> | Straight aluminum back cane | 18" - 21" increment of 1/2" | Set at ² : | J |
| BC12-1315 | <input type="checkbox"/> | 8° bend aluminum back cane | 13.5" - 15" increment of 1/2" | Set at ² : | OTP |
| BC12-1518 | <input type="checkbox"/> | 8° bend aluminum back cane | 15" - 18" increment of 1/2" | Set at ² : | OTP |
| BC12-1821 | <input type="checkbox"/> | 8° bend aluminum back cane | 18" - 21" increment of 1/2" | Set at ² : | OTP |

| ANGLE AND HEIGHT ADJUSTABLE BACK CANE WITH PUSH HANDLE OPTIONS (MUST select ONE push handle options) | | | | | |
|--|--------------------------|-----------------------------|--|-----------------------|-----|
| BC13-1518 | <input type="checkbox"/> | Straight aluminum back cane | 15" - 18" increment of 1/2" | Set at ² : | J |
| BC13-1821 | <input type="checkbox"/> | Straight aluminum back cane | 18" - 21" increment of 1/2" | Set at ² : | J |
| BC14-1518 | <input type="checkbox"/> | 8° bend aluminum back cane | 15" - 18" increment of 1/2" | Set at ² : | OTP |
| BC14-1821 | <input type="checkbox"/> | 8° bend aluminum back cane | 18" - 21" increment of 1/2" | Set at ² : | OTP |
| | | Select back cane angle: | 85° ¹ <input type="checkbox"/> 90° <input type="checkbox"/> 95° STD <input type="checkbox"/> 100° <input type="checkbox"/> 105° <input type="checkbox"/> 110° <input type="checkbox"/> | | |

| PUSH HANDLES OPTIONS (ONE option at a time) | | | | |
|---|--------------------------|---|--|-----|
| PH01 | <input type="checkbox"/> | Push handles | | NC |
| PH05 | <input type="checkbox"/> | Fold down push handles ^{3,5} | | OTP |
| PH06-920 | <input type="checkbox"/> | Clamp on height adjustable push handles 9"-20" ^{3,4,5} | | OTP |
| PH06-923 | <input type="checkbox"/> | Clamp on height adjustable push handles 9"-23" ^{3,4,5} | | OTP |
| PH02 | <input type="checkbox"/> | Omit push handles | | NC |

| STROLLER HANDLE AND STABILIZER BAR (only available with push handle) | | | | |
|--|--------------------------|--|--|-----|
| PH04 | <input type="checkbox"/> | Stroller handle (not available with the HD option) | | OTP |
| PH03 | <input type="checkbox"/> | Newton folding stabilizer bar (not available with stroller handle) | | OTP |

1- Not compatible with 8 degree bent back cane; 2- If not indicated, default height setting is at the lowest position; measured from seat sling to top of back upholstery; 3- 265lb weight limit

4- Not compatible with swing away armrests, 8° bend back canes, 21-24" back canes and amputee axle plates; 5- Not compatible with stroller handler, stabilizer bar, headrest and attendant lock;

| BACK UPHOLSTERY | | | | |
|-----------------|--------------------------|--|---------------|-----|
| BH05 | <input type="checkbox"/> | Slip-on Nylon back upholstery | | NC |
| BH06 | <input type="checkbox"/> | Adjustable tension Nylon back upholstery | | OTP |
| BH99 | <input type="checkbox"/> | Omit Back upholstery | | NC |
| | <input type="checkbox"/> | NXT back Support | See pricelist | OTP |

| SEAT CUSHION | | | | |
|--------------|--------------------------|-------------------|----------------|-----|
| SC01 | <input type="checkbox"/> | 2" Cushion | | OTP |
| SC02 | <input type="checkbox"/> | 3" Cushion | | OTP |
| SC99 | <input type="checkbox"/> | Omit seat cushion | | NC |
| | <input type="checkbox"/> | NXT cushion | See price list | OTP |

| Rear wheels | | | | | | | |
|--|--------------------------|--|---|--|--|---|---|
| ONE ARM DRIVE¹ <i>Only available with Newton One rear wheel, permanent axles and 0° camber</i> | | | | | | | |
| HR22 | <input type="checkbox"/> | One arm drive - aluminum inner handrim ^{2,3} | 24" | Left <input type="checkbox"/> | Right <input type="checkbox"/> | | J |
| HR60 | <input type="checkbox"/> | One arm drive - plastic coated inner handrim ^{2,3} | 24" | Left <input type="checkbox"/> | Right <input type="checkbox"/> | | OTP |
| HR98 | <input type="checkbox"/> | Omit handrim on opposite side of the One Arm Drive (OAD) | | | | | OTP |
| REAR WHEELS | | | | | | Available | |
| RW01 | <input type="checkbox"/> | Mag ⁴ | | | | 20", 22" 24" | OTP |
| RW02 | <input type="checkbox"/> | Newton One - spoke wheel ⁵ | | | | 20", 22" 24" | NC |
| RW03 | <input type="checkbox"/> | Newton Gravity - ultralight wheel | | | | 20", 22", 24", 25", 26" | OTP |
| RW04 | <input type="checkbox"/> | Spinergy Spox Blk STD <input type="checkbox"/> | Wht ⁶ <input type="checkbox"/> | Blue ⁶ <input type="checkbox"/> | Red ⁶ <input type="checkbox"/> | Yel ⁶ <input type="checkbox"/> | 22", 24", 25", 26" |
| RW05 | <input type="checkbox"/> | Spinergy LX Blk STD <input type="checkbox"/> | Pur ⁶ <input type="checkbox"/> | Wht ⁶ <input type="checkbox"/> | Blue ⁶ <input type="checkbox"/> | Red ⁶ <input type="checkbox"/> | Yel ⁶ <input type="checkbox"/> |
| RW07 | <input type="checkbox"/> | Spinergy CLX ⁷ Blk STD <input type="checkbox"/> | Pur ⁶ <input type="checkbox"/> | Wht ⁶ <input type="checkbox"/> | Blue ⁶ <input type="checkbox"/> | Red ⁶ <input type="checkbox"/> | Yel ⁶ <input type="checkbox"/> |
| TIRES | | | | | | Available | |
| Solid | | | | | | | |
| TI01 | <input type="checkbox"/> | Soft Urethane 1 3/8" | | | | 20", 22" 24" | NC |
| TI02 | <input type="checkbox"/> | Soft Urethane knobby 1 3/8" ⁸ | | | | 22", 24", 25", 26" | J |
| TI04 | <input type="checkbox"/> | Soft Urethane 1" - Shox | | | | 22", 24", 25", 26" | OTP |
| Pneumatic | | | | | | | |
| TI05 | <input type="checkbox"/> | Pneumatic 1 3/8" ¹¹ | | | | 20", 22", 24", 25", 26" | NC |
| TI08 | <input type="checkbox"/> | Pneumatic with Airless insert 1 3/8" ⁹ | | | | 22", 24", 26" | OTP |
| TI06 | <input type="checkbox"/> | Pneumatic HP, Low Tread, Puncture resistant, black 1" - SpeedLite | | | | 20", 22", 24", 25", 26" | OTP |
| TI07 | <input type="checkbox"/> | Pneumatic HP, Medium Tread, Puncture resistant, black 1" - TrailBlazer | | | | 24", 25", 26" | OTP |

1- Offered with handrims on each side of the wheelchair; select the outer handrim in the handrims section; 2- Only standard handrim position available; 3- Not available with HD option

4- Not compatible with HP tires; Only available with aluminum or plastic coated handrim, standard position; 5- Not compatible with Shox tires; 6- color spokes require an additional 10 days lead-time;

7- Only available with 1" tires; 8- 22" is only available with Mags and Newton One rear wheels; 9- Not available with Spinergy CLX, Spinergy LX 25", 26" and Spox 25", 26" rear wheels

| Handrims | | | | | | | |
|-------------------------------|--------------------------|--|---|--|--|-------------------------|-----|
| HANDRIM | | | | | | Available | |
| HR01 | <input type="checkbox"/> | Aluminum anodized | | | | 20", 22", 24", 25", 26" | NC |
| HR61 | <input type="checkbox"/> | Aluminum black hard anodized ² | | | | 20", 22", 24", 25" | OTP |
| HR02 | <input type="checkbox"/> | Plastic coated ¹ | | | | 20", 22", 24", 25", 26" | OTP |
| HR03 | <input type="checkbox"/> | High friction coated ^{1,2,3} | | | | 22", 24", 25", 26" | OTP |
| HR07-HR18 and HR65-HR71 | <input type="checkbox"/> | Newton Air Grip ² | <i>See page 6 for the color selection and price</i> | | | 20", 22", 24", 25", 26" | J |
| HR28 | <input type="checkbox"/> | Surge ^{1,2,3} (1 1/2" Oval handrim w/ Gripton high friction strip) | | | | 22", 24", 25", 26" | OTP |
| HR05 | <input type="checkbox"/> | Surge LT ^{1,2,3} (1 1/8" Oval handrim w/ Gripton high friction strip) | | | | 22", 24", 25", 26" | OTP |
| HR04 | <input type="checkbox"/> | Natural Fit ^{1,2,3} | | | | 22", 24", 25", 26" | OTP |
| HR62 | <input type="checkbox"/> | Simi H ^{1,2,3} (1 1/4" Oval handrim with high friction strip) | | | | 22", 24", 25", 26" | OTP |
| HR63 | <input type="checkbox"/> | Nova H ^{1,2,3} (1 1/4" Oval handrim with high friction strip) | | | | 22", 24", 25", 26" | OTP |
| HR64 | <input type="checkbox"/> | Optimum H ^{1,2,3} (1 1/8" heart-shaped handrim) | | | | 22", 24", 25", 26" | OTP |
| HR99 | <input type="checkbox"/> | Omit handrim | | | | | NC |


1- Only standard and narrow handrim position. By default, the tab won't be cut with the narrow position; 2- Not available with Mag wheels; 3 - Not available with one arm drive;

| Handrims option | | | | | | | |
|--|--------------------------|---|--|---|--|--|-----|
| ASSEMBLY POSITION | | | | | | | |
| HR29 | <input type="checkbox"/> | Standard Handrim position | Full tab | | | | NC |
| HR030 | <input type="checkbox"/> | Narrow Handrim position no cut | Full tab | | | | NC |
| HR30 | <input type="checkbox"/> | Narrow Handrim position with cut ³ | Short tab 2 positions | | | | J |
| HR31 | <input type="checkbox"/> | Super Narrow Handrim ³ | Short tab 2 positions STD <input type="checkbox"/> | Short tab 1 position <input type="checkbox"/> | | | J |
| THUMB PIECE SELECTION FOR NATURAL FIT, SURGE, SURGE LT HANDRIMS | | | | | | | |
| HR23 | <input type="checkbox"/> | Standard grip | | | | | OTP |
| HR27 | <input type="checkbox"/> | Super grip | | | | | OTP |
| HR099 | <input type="checkbox"/> | Omit thumb piece | | | | | OTP |
| 3- Only available with Aluminum and Air Grip handrims; | | | | | | | |
| AXLE | | | | | | | |
| AX01 | <input type="checkbox"/> | Quick release axle ¹ | | | | | NC |
| AX02 | <input type="checkbox"/> | Permanent axle | | | | | J |
| AX03 | <input type="checkbox"/> | Quad release axle ¹ | | | | | OTP |
| AXLE PLATE | | | | | | | |
| AX04 | <input type="checkbox"/> | Amputee adjustable axle plate ² | | | | | OTP |

1- Not required with one arm drive; 2 - May interfere with swing away armrest and limit seat to floor height

| REAR WHEEL CAMBER | | | |
|-------------------|--------------------------|-----------|----|
| CM00 | <input type="checkbox"/> | 0° camber | NC |
| CM03 | <input type="checkbox"/> | 3° camber | NC |

CENTER OF GRAVITY



Choose position of rear wheel axle plate:
 Measure distance from front of back post to center of axle receiver.
 Default setting is at 1 1/4"

| Most stable | | | | | | Most responsive |
|--------------------------|--------------------------|--------------------------|--------------------------|--------------------------|--------------------------|-----------------|
| AMPUTEE ¹ | 3/4" | 1" 1/4 | 1" 3/4 | 2" 1/4 | 2" 3/4 | |
| <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | |

Motion Composites will select the closest possible center of gravity (COG) if an issue arises with the COG

1- Only available with amputee axle plate

| WHEEL LOCK | | | |
|------------|--------------------------|--|-----|
| WL08 | <input type="checkbox"/> | Newton Wheel lock - push to lock | NC |
| WL14 | <input type="checkbox"/> | 6" removable extension handle for push to lock | J |
| WL16 | <input type="checkbox"/> | Aluminum push to lock with extensions | NC |
| WL02 | <input type="checkbox"/> | Pull to lock | NC |
| WL04 | <input type="checkbox"/> | Newton grade aid push to lock (works best with pneumatic or high pressure tire) | OTP |
| WL13 | <input type="checkbox"/> | 6" removable extension handle for pull to loc and grade aid | J |
| WL05 | <input type="checkbox"/> | Scissors Lock | OTP |
| WL06 | <input type="checkbox"/> | Attendant Lock (additional set of wheel lock mounted to the back) | OTP |
| WL15 | <input type="checkbox"/> | Unilateral wheel lock - pull to lock ¹ Left <input type="checkbox"/> Right <input type="checkbox"/> | OTP |
| WL99 | <input type="checkbox"/> | Omit wheel locks | NC |

1- For more information about incompatibilities and restriction, refer to the table at page 7 and the "How-to documents" page of our website:
https://www.motioncomposites.com/en_ca/support-and-education/how-to-documents

| Armrests | | | |
|---|--------------------------|--|-----|
| HEIGHT ADJUSTABLE FLIP BACK ARMREST (Convertible to "T" armrest) ^{1,4} | | | |
| AR01-812 | <input type="checkbox"/> | 10" Desk length armpad 8" - 12" Locked <input type="checkbox"/> Unlocked STD <input type="checkbox"/> | NC |
| AR01-1014 | <input type="checkbox"/> | 10" Desk length armpad 10" - 14" Locked <input type="checkbox"/> Unlocked STD <input type="checkbox"/> | NC |
| AR02-812 | <input type="checkbox"/> | 14" Full length armpad 8" - 12" Locked <input type="checkbox"/> Unlocked STD <input type="checkbox"/> | NC |
| AR02-1014 | <input type="checkbox"/> | 14" Full length armpad 10" - 14" Locked <input type="checkbox"/> Unlocked STD <input type="checkbox"/> | NC |
| HEIGHT ADJUSTABLE "T" ARMREST ¹ | | | |
| AR13-610 | <input type="checkbox"/> | 10" Desk length armpad ⁵ 6" - 10" | NC |
| AR13-812 | <input type="checkbox"/> | 10" Desk length armpad 8" - 12" | NC |
| AR13-1014 | <input type="checkbox"/> | 10" Desk length armpad 10" - 14" | NC |
| AR14-610 | <input type="checkbox"/> | 14" Full length armpad ⁵ 6" - 10" | NC |
| AR14-812 | <input type="checkbox"/> | 14" Full length armpad 8" - 12" | NC |
| AR14-1014 | <input type="checkbox"/> | 14" Full length armpad 10" - 14" | NC |
| SWING AWAY ARMREST ² | | | |
| AR05 | <input type="checkbox"/> | Tubular armrest - Short pad 8" - 11" | J |
| AR23 | <input type="checkbox"/> | Tubular armrest - long pad 8" - 11" | J |
| AR06 | <input type="checkbox"/> | 10" Desk length flat armpad 8" - 11" | J |
| AR17 | <input type="checkbox"/> | 14" Full length flat armpad 8" - 11" | J |
| ARMREST OPTIONS | | | |
| AR12 | <input type="checkbox"/> | 14" Full Length armpad - Gel Ovation (pair) ³ | OTP |
| AR99 | <input type="checkbox"/> | Omit armrest | J |

1- May have 1/2" adjustment restriction on both limits of the range; 2- Could interfere with some rigid backrests; Not available with attendant lock and fixed carbon fiber side guards;
 3- Only available with full length armrest; Not available with tubular (short and long) and short armrest; 4- Not available with attendant lock; 5- May have some restriction with seat-to-floor height and rear wheel

| SIDE GUARDS (not available with Flip Back and "T" Armrest) | | | |
|--|--------------------------|--|-----|
| SG01 | <input type="checkbox"/> | Plastic side guards (removable) | OTP |
| SG02 | <input type="checkbox"/> | Carbon fiber side guards (fixed) | OTP |
| SG03 | <input type="checkbox"/> | Carbon fiber side guards (removable) | OTP |
| SG06 | <input type="checkbox"/> | Plastic fender side guards - straight bracket (removable) | OTP |
| SG08 | <input type="checkbox"/> | Plastic fender side guards - offset bracket (removable) ¹ | OTP |
| SG04 | <input type="checkbox"/> | Carbon fiber fender side guards (removable) | OTP |
| SG99 | <input type="checkbox"/> | Omit side guard | NC |
| SIDE GUARDS OPTION | | | |
| SG07 | <input type="checkbox"/> | Side guards clip (pair) ² | NC |

1- only compatible with 0° camber; Increase distance between fender side guards by 1 1/8"; 2- Not available with fixed carbon fiber side guard

| POSITIONING BELT | | | |
|------------------|--------------------------|---|-----|
| SB01-S | <input type="checkbox"/> | Velcro adjustable - Standard 35" ¹ | OTP |
| SB01-L | <input type="checkbox"/> | Velcro adjustable - Long 60" | OTP |
| SB02-S | <input type="checkbox"/> | Auto buckle - Standard 35" ¹ | NC |
| SB02-L | <input type="checkbox"/> | Auto buckle - Long 60" | NC |
| SB04-M | <input type="checkbox"/> | BodyPoint Hip Belt - 2 point not padded - Medium 56" | OTP |
| SB04-L | <input type="checkbox"/> | BodyPoint Hip Belt - 2 point not padded - Long 61" | OTP |
| SB05-S | <input type="checkbox"/> | BodyPoint Hip Belt - 2 point padded - Small 51" | OTP |
| SB05-M | <input type="checkbox"/> | BodyPoint Hip Belt - 2 point padded - Medium 56" | OTP |
| SB05-L | <input type="checkbox"/> | BodyPoint Hip Belt - 2 point padded - Long 61" | OTP |
| SB06-S | <input type="checkbox"/> | BodyPoint Hip Belt - 4 point padded - Small 51" | OTP |
| SB06-M | <input type="checkbox"/> | BodyPoint Hip Belt - 4 point padded - Medium 56" | OTP |
| SB06-L | <input type="checkbox"/> | BodyPoint Hip Belt - 4 point padded - Long 61" | OTP |
| SB03 | <input type="checkbox"/> | Hardware attachment for 2 extra points (1 pair) | OTP |
| SB08-M | <input type="checkbox"/> | BodyPoint EVOFLEX® Positioning Belt Rehab latch and Band Clamps - Medium 18" | OTP |
| SB08-L | <input type="checkbox"/> | BodyPoint EVOFLEX® Positioning Belt Rehab latch and Band Clamps - Long 24" | OTP |
| SB99 | <input type="checkbox"/> | Omit positioning belt | NC |

1- Not available with wheelchair width of 18" and more

| HEADREST | | | |
|----------|--------------------------|---|-----|
| AC01-S | <input type="checkbox"/> | Profiled Headrest - Small (3.5"X6") | OTP |
| AC01-M | <input type="checkbox"/> | Profiled Headrest - Medium (4.5"X7") | OTP |
| AC01-L | <input type="checkbox"/> | Profiled Headrest - Large (5.5"X8") | OTP |
| AC28 | <input type="checkbox"/> | Headrest mounting hardware with removable non folding stabilizer bar ¹ | OTP |

1- Only available with push handles - Not available with a stroller handle or a folding stabilizer bar

| ACCESSORIES | | | |
|-------------|-------------------------------------|---|-----|
| AC03 | <input checked="" type="checkbox"/> | Anti-tippers | NC |
| AC29 | <input type="checkbox"/> | Swing-away anti-tipper ¹ Left <input type="checkbox"/> Right <input type="checkbox"/> | OTP |
| AC27 | <input type="checkbox"/> | Tip assist ² | OTP |
| AC06 | <input type="checkbox"/> | Cane and crutch holder Left <input type="checkbox"/> Right <input type="checkbox"/> | OTP |
| AC07 | <input type="checkbox"/> | Oxygen tank holder ⁴ - D and E Type - <i>Installed to the left</i> | OTP |
| AC08 | <input type="checkbox"/> | Spoke guards ³ Available: 20", 22", 24", 26" | OTP |
| AC09 | <input type="checkbox"/> | Footrest neoprene impact guard (<i>pair</i>) - Black | OTP |
| AC10 | <input type="checkbox"/> | Seat pouch | OTP |
| AC30 | <input type="checkbox"/> | Newton multi-purpose pouch | OTP |
| AC26 | <input type="checkbox"/> | BodyPoint Mobility Bag | OTP |
| AC23 | <input type="checkbox"/> | Newton Backpack | OTP |
| AC12 | <input type="checkbox"/> | Velcro Closing Strap | OTP |
| AC13 | <input type="checkbox"/> | Tool kit | OTP |
| AC16 | <input type="checkbox"/> | Motion Composites Polo Shirt W/S <input type="checkbox"/> W/M <input type="checkbox"/> W/L <input type="checkbox"/> M/S <input type="checkbox"/> M/M <input type="checkbox"/> M/L <input type="checkbox"/> M/XL <input type="checkbox"/> M/XXL <input type="checkbox"/> M/XXXL <input type="checkbox"/> | OTP |


1- Must select the pair (left and right) with HD option; Only available with rear seat to floor height between 13 1/2" and 19 3/4"; 2- Cannot be combined with Anti Tippers

3- Not available with Mag wheels and Spinergy; 4- Not compatible with swing away armrest, amputee axle plate and WC-19 transit tie-down

| Colors | | | | | | | | | | | | | | | | | | | | |
|----------------------|--------------------------|--------------------------|--------------------------|--------------------------|--------------------------|--------------------------|--------------------------|--------------------------|--------------------------|--------------------------|--------------------------|--------------------------|--------------------------|--------------------------|--------------------------|--------------------------|--------------------------|--------------------------|--------------------------|-----|
| Options ¹ | Black | Sunkissed Orange | Burgundy | Sapphire Blue | Monster Green | Charcoal | Fuchsia | Steel Blue | Ferrari Red | Acid Green | Electric Purple | Caribbean Blue | White | Pink Pearl | Plum Purple | Sky Blue | Black Cherry | Khaki Green (matte) | Desert Sand (matte) | |
| AirGrip | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | OTP |
| Frame | <input type="checkbox"/> | | | | | | | | | | | | | | | | | | | NC |

1- Color representation may vary from one monitor to another. Therefore, the actual paint color on your wheelchair might differ slightly from what you see on your screen.; Finish between Airgrip and frame might be different;

Fork and Stem bolt combinations



Unilateral wheel lock restrictions

| Seat depth: shall be 16 in and greater | | |
|---|-----------------|------------------------------|
| Rear wheel: shall be 24 in and less | | |
| "T" or flip-back armrest only compatible with 0° Camber | | |
| One arm drive: Not compatible with "T" or flip-back armrest | | |
| "T" or flip-back armrest may require to move the rear wheels outwards | | |
| Not compatible with wheel lock lever extension | | |
| Rear wheel diameter | Seat depth (in) | COG Compatibility Range (in) |
| 20 in | 16+ | 1.25 to 2.75 |
| | 16 | 0.75 to 2.25 |
| 22 in | 17+ | 0.75 to 2.75 |
| | 16 | 0.75 to 1.75 |
| 24 in | 17 | 0.75 to 2.25 |
| | 18+ | 0.75 to 2.75 |

Note :